



WFDP84NPSW

20A Double Pole Switch with LED Indicator Polished Steel White Insert

Technical Features

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour Silver

Surface finish Glossy

Material Stainless steel

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm

Built-in depth 27.90 mm

Electric current

Rated current 20 A

Texts

Lighting With control LED for ON

Push button No

Imprint With clear terminal markings