



47506086

SCHUKO soc. out., Q.x, ant. velvety, lacq.

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Anthracite

RAL code 7021

Surface finish Velvety

Material Duroplastic

Treatment Varnished

Dimensions

Height 71 mm

Width 71 mm

Number of units 1

Built-in depth flush-mounted boxes 31 mm

Built-in depth 32 mm

Connection

Connector/plug type Plug-in terminal

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Plug-in connection

Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field Yes

Capacity

Number of modules 1

Safety

With enhanced contact protection No

Impact resistance IK IK02

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals
Labelling	With labelling field

Suitable for

Q.x

Sustainability

Halogen free	Yes
RoHS conform	Yes