



EG203E



Digital time switch weekly cycle 2 channels Evolution

Technical Features

Frequency

Frequency 50 - 60 Hz

Power

230 V incandescent and halogen lamp 2300 W

Functions

Power reserve in years 5 y
 With network synchronisation No
 With quartz synchronisation Yes
 Number of function channels 2

Equipment

Accuracy per day 1.50 s
 With impulse programme Yes
 Number of channels 2

Connection

Type of contacts 2x changeovers

Settings

Daily programme No
 Weekly programme Yes
 Annual programme No

Use conditions

Operating temperature -5 - 45 °C

Connection

Cross-section flexible conductor 1 - 16 mm²
 Cross-section rigid conductor 1.5 - 10 mm²

Texts

Type of connection With screw terminals
 Function Keylock by means of blocking key

Dimensions

Height 85 mm
 Width 35 mm
 Depth 64 mm

Main electrical attributes

Minimum interval between 2 switching times 1 min

Capacity

Number of modules 2