



EG203E



Digital time switch weekly cycle 2 channels Evolution

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

230 V incandescent and halogen lamp	2300 W
-------------------------------------	--------

Functions

Power reserve in years	5 y
With network synchronisation	No
With quartz synchronisation	Yes
Number of function channels	2

Equipment

Accuracy per day	1.50 s
With impulse programme	Yes
Number of channels	2

Connection

Type of contacts	2x changeovers
------------------	----------------

Settings

Daily programme	No
Weekly programme	Yes
Annual programme	No

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Connection

Cross-section flexible conductor	1 - 16 mm ²
Cross-section rigid conductor	1.5 - 10 mm ²

Texts

Type of connection	With screw terminals
Function	Keylock by means of blocking key

Dimensions

Height	85 mm
Width	35 mm
Depth	64 mm

Main electrical attributes

Minimum interval between 2 switching times	1 min
--	-------

Capacity

Number of modules	2
-------------------	---