



75141134



IP20

KNX glass sensor 1gang comf, intg bus coupling unit, KNX - TS sensor, glass al.

Technical Features

Installation, mounting

Mounting on Flush mounting

Use conditions

Operating temperature -5 - 45 °C

Functions

With room temperature controller Yes

Power

Current consumption 12.50 mA

Dimensions

Built-in depth 24.20 mm  
Built-in depth flush-mounted boxes 27 mm  
Height 160 mm  
Width 86 mm  
Depth 37.70 mm

Equipment

Number of actuation points 2

Controls and indicators

With LED indication Yes

Materials

Colour Aluminium  
RAL code 9006  
Material Aluminium  
Glass  
Surface finish Glossy

Accessories

Has labelling field No

Screen

With display No

Texts

Function For switch, push-button, dimmer and shutter functions  
Blocking function for sensor surface e.g. for cleaning the glass surface  
Installation mode For vertical mounting  
Temperature Additional connection for external temperature sensor  
Integrated temperature sensor for operation as controller extension  
unit  
Temperature measurement via internal Temperature sensor or external  
communication object

Sustainability

REACH-SVHC free Yes  
RoHS conform Yes