



WNA401

cubyko Single flush adapter composable grey IP55

Technical Features

Capacity

Number of gangs	1
Number of modules	1

Materials

Colour	Light grey
RAL code	7035
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	83 mm
Width	83 mm
Depth	39 mm
Number of units horizontal	1
Number of units vertical	1

Accessories

Has labelling field	No
---------------------	----

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Installation mode	With clamp/screw fastening With mounting adapter and sealing For flush-mounted and hollow wall mounting
-------------------	---

Sustainability

REACH-SVHC free	Yes
-----------------	-----