



HWX712H

**Spring charging motor 48V DC HW2/4 (MO)**

**Technical Features**

**Electric current**

Rated current	4.20 A
---------------	--------

**Voltage**

Type voltage supply	DC
Rated insulation voltage $U_i$	450 V
Rated impulse withstand voltage $U_{imp}$	6000 V
Command voltage DC	48 - 48 V

**Use conditions**

Operating temperature	-25 - 70 °C
-----------------------	-------------

**Functions**

With auto reset function	No
--------------------------	----

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes