



47063515

**SCHUKO soc.out. insert hinged cover surf./flushmtd,enhncd contact prot.,W1,gre**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Use conditions**

Operating temperature -15 - 30 °C

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Grey

RAL code 7011

Surface finish Matt

Material Thermoplastic

Treatment Untreated

**Dimensions**

Height 71 mm

Width 71 mm

Built-in depth flush-mounted boxes 0 mm

**Installation, mounting**

Mounting on Flush mounting  
Surface mounting

**Connectivity**

Type of connection Plug-in connection

Mounting type Screw mounting  
Claw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid Yes

With round protective earth pin No

With signal lamp No

With lock No

**Accessories**

Has labelling field No

**Cover, door**

Type of lid Self-closing hinged cover, can be arrested in end position

**Capacity**

Number of modules 1

**Safety**

With enhanced contact protection No

Impact resistance IK IK05

Ingress Protection (IP) class IP55

**Functions**

With orientation lighting No

With function lighting No

**Identification**

With imprint No

---

**Texts**

Cover	Complete housing
Protection	Enhanced contact protection
Type of connection	With plug-in terminals

---

**Sustainability**

Halogen free	Yes
RoHS conform	Yes