



VS312PM

Small distributor,golf,surface,3row,IP40,36M,MS-terminal,N+PE,white door

### Technical Features

#### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 400 - 400 V |
|-----------------|-------------|

#### Installation, mounting

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

#### Electric current

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

#### Equipment

|                            |     |
|----------------------------|-----|
| Number of rails            | 3   |
| Number of rows             | 3   |
| Number of section in width | 1   |
| With lock                  | No  |
| Has neutral terminal block | Yes |

#### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 36 |
|-------------------|----|

#### Functions

|                     |     |
|---------------------|-----|
| With conduit inlets | Yes |
|---------------------|-----|

#### Dimensions

|        |        |
|--------|--------|
| Height | 500 mm |
| Width  | 282 mm |
| Depth  | 99 mm  |

#### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
| Number of locks         | 0 |

#### Dimensions

|                       |    |
|-----------------------|----|
| Number of width units | 12 |
|-----------------------|----|

#### Cover, door

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

#### Materials

|          |            |
|----------|------------|
| Material | Plastic    |
| RAL code | 9010       |
| Colour   | Pure white |

#### Equipment

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate          | No  |

#### Materials

|                       |    |
|-----------------------|----|
| Ultraviolet-resistant | No |
|-----------------------|----|

#### Safety

|                               |                              |
|-------------------------------|------------------------------|
| Protection class              | Isolation class II           |
| Impact resistance IK          | IK07                         |
| Ingress Protection (IP) class | IP40                         |
| Locking type                  | Snap on lock<br>Without lock |
| Glow wire test                | 650 °C                       |

#### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|