



48031909

**SCHUKO socket outlet/USB A-A, S.1/B.x, polar white matt**

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Output current	2400 mA
Rated current	16 A

**Voltage**

Output voltage	4.75 - 5.25 V
----------------	---------------

**Use conditions**

Operating temperature	5 - 35 °C
-----------------------	-----------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Power**

Output power	12 W
Power consumption standby	0.05 W

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	71 mm
Width	71 mm
Depth	45 mm
Number of units	1
Built-in depth flush-mounted boxes	40 mm
Built-in depth	32 mm

**Connection**

Connector/plug type	Plug-in terminal
---------------------	------------------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting
Connector/plug type USB	AA

**Equipment**

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	1
-------------------	---

---

**Safety**

With enhanced contact protection	Yes
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

---

**Functions**

With orientation lighting	No
With function lighting	No

---

**Identification**

With imprint	No
--------------	----

---

**Texts**

Fuse	Short-circuit and overload-proof (electronic fuse)
Cover	Central cover plate
Connectors jacks	With 2 USB sockets type A
Type of connection	With plug-in terminals

---

**Suitable for**

S.x/B.x
---------

---

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes