



WNA105



IP55

cubyko Socket 2P+E detrompage composable grey IP55

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current	16 A
---------------	------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Polycarbonate (PC) Polypropylene (PP)
Treatment	Untreated
Contains recycled material (% of total plastic weight)	0 %

Dimensions

Height	75 mm
Width	75 mm
Depth	22.80 mm
Number of units	1
Built-in depth flush-mounted boxes	35 mm
Built-in depth	22 mm
Height of P-touch band for labelling field	12 mm

Connection

Connector/plug type	Turn screw lock
Cross-section flexible conductor without wire end sleeve	1.0 - 2.5 mm ²

Installation, mounting

Mounting on	Flush mounting Surface mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Plug-in connection
With claw mounting	No
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No
With lock	No

Accessories

Has labelling field	Yes
Pre-equipped with	Socket outlet

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	Yes
----------------------------------	-----

Impact resistance IK	IK07
----------------------	------

Ingress Protection (IP) class	IP55
-------------------------------	------

Usable in higher IP class	IP55 with closed cover
---------------------------	------------------------

Functions

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

Identification

With imprint	No
--------------	----

Texts

Imprint	Without imprint
---------	-----------------

Cover	For covering of socket outlets
-------	--------------------------------

Protection	Without protective screen
------------	---------------------------

Type of connection	With plug-in terminals
--------------------	------------------------

Labelling	Without labelling
-----------	-------------------

Suitable for

cubyko	
--------	--

Sustainability

REACH-SVHC free	Yes
-----------------	-----
