




260219



230 V USB charging socket outlet, 2gang, 3.0A, round supporting ring, pw.

Technical Features

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Dimensions

Built-in depth	32 mm
Built-in depth flush-mounted boxes	34 mm

Equipment

Number of outputs	2
-------------------	---

Accessories

Has labelling field	No
With miniature fuse	No

Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt

Power

Output power	15 W
Power consumption standby	0.15 W

Voltage

Input voltage	230 - 230 V
Output voltage	5 - 5 V

Electric current

Rated current	0.20 A
Output current	3000 mA

Texts

Connectors jacks	With 2 USB sockets type A
Fuse	Short-circuit and overload-proof (electronic fuse)
Type of connection	With screw terminals
Protection	Without enhanced contact protection

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes