



EC100

**Hours counter**

**Technical Features**

**Capacity**

Number of modules	2
-------------------	---

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Use conditions**

Operating temperature	-10 - 45 °C
Storage/transport temperature	-20 - 60 °C

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Connection**

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>

**Dimensions**

Height	90 mm
Width	35 mm
Depth	60 mm

**Power supply**

Supply voltage	230 V +/- 15%
----------------	---------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Installation, mounting**

Mounting on	DIN rail
-------------	----------

**Equipment**

Number of channels	6
--------------------	---

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes