



VS312TM

Small distributor,golf,surface,3row,IP40,36M,MS-terminal,N+PE,transparent door

**Technical Features**

**Voltage**

Nominal voltage	400 - 400 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	63 A
---------------	------

**Equipment**

Number of rails	3
Number of rows	3
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

**Capacity**

Number of modules	36
-------------------	----

**Functions**

With conduit inlets	Yes
---------------------	-----

**Dimensions**

Height	500 mm
Width	282 mm
Depth	99 mm

**Cover, door**

Number of cabinet doors	1
Number of locks	0

**Dimensions**

Number of width units	12
-----------------------	----

**Cover, door**

Door/cover is transparent	Yes
---------------------------	-----

**Materials**

Material	Plastic
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Materials**

Ultraviolet-resistant	No
-----------------------	----

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock Without lock
Glow wire test	650 °C

**Sustainability**

RoHS conform	Yes
--------------	-----