



384603



Spring-return push-button, change-over contact, Serie 1930/Glas/R.classic

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Short rotary handle
Number of poles	1

Materials

Material	Metal Plastic
Transparent	No

Dimensions

Height	71 mm
Width	71 mm
Depth	42 mm
Built-in depth flush-mounted boxes	35 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	0
Type of push button	Single push button
With feedback signal contact	No

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Accessories

Has labelling field	No
---------------------	----

Texts

Imprint	Without imprint
Type of connection	With screw terminals

Suitable for

Serie 1930 / Serie Glas / Serie R.classic

Sustainability

RoHS conform	Yes
--------------	-----