



384600



Spring-return push-button, change-over contact, Serie 1930/Glas/R.classic

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Architecture

Control/operation element Short rotary handle

Number of poles 1

Materials

Surface finish Matt

Material Metal
Plastic

Treatment Untreated

Transparent No

Dimensions

Height 71 mm

Width 71 mm

Depth 42 mm

Diameter 71 mm

Installation, mounting

Mounting on Flush mounting

Controls and indicators

Number of buttons 0

Type of push button Single push button

With feedback signal contact No

Safety

Ingress Protection (IP) class IP20

Accessories

Has labelling field No

Texts

Imprint Without imprint

Installation mode With spreader claws

Switch mode Change-over contact

Type of connection With screw terminals