



47271909

**SCHUKO soc. out. 45°, S.1/B.3/B.7, p. white, matt, plastic**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Polar white

RAL code 9010

Surface finish Matt

Material Thermoplastic

Treatment Untreated

**Dimensions**

Height 71 mm

Width 71 mm

Number of units 1

Built-in depth 32 mm

**Connection**

Connector/plug type Plug-in terminal

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Plug-in connection

Mounting type Screw mounting

Claw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO

Rotated central insert Yes

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 1

**Safety**

With enhanced contact protection No

Impact resistance IK IK05

Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No

With function lighting No

**Identification**

With imprint No

---

**Texts**

|                    |                                     |
|--------------------|-------------------------------------|
| Cover              | Central cover plate                 |
| Protection         | Without enhanced contact protection |
| Type of connection | With plug-in terminals              |

---

**Suitable for**

S.x/B.x

---

**Sustainability**

|              |     |
|--------------|-----|
| Halogen free | Yes |
| RoHS conform | Yes |