



WMPS16WG

### Intermediate Switch Wide Rocker Grey

#### Technical Features

##### Electric current

Switching current	10 A
-------------------	------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Materials

Colour	Grey
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

##### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Controls and indicators

Number of buttons	1
-------------------	---

##### Dimensions

Dimensions	86 x 86 mm
Built-in depth	13.10 mm

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Architecture

Control/operation element	Single rocker
---------------------------	---------------

##### Electric current

Rated current	10 A
---------------	------

##### Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	Intermediate

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes