

Orange LED Indicator light 230VAC

Technical Features

Capacity

Number of modules

1

Frequency

Frequency

50 - 60 Hz

Voltage

Rated insulation voltage U_i

250 V

Rated impulse withstand voltage U_{imp}

4000 V

Rated operational voltage U_e

230 - 230 V

Type voltage supply

AC

Use conditions

Operating temperature

-20 - 50 °C

Storage/transport temperature

-40 - 80 °C

Connectivity

Type of connection

Screw terminal

Connection

Cross-section flexible conductor

0.75 - 6 mm²

Cross-section rigid conductor

0.75 - 10 mm²

Power

Total power loss under IN

0.80 W

Dimensions

Height

83 mm

Width

17.50 mm

Depth

62 mm

Lighting

Type of lamp

LED

Connection

Type of lamp socket

Fix

Materials

Colour

Orange

Safety

Ingress Protection (IP) class

IP20

Power

Power per charging point

0 kW

Sustainability

REACH-SVHC free

Yes

RoHS conform

Yes