



WXPSS82

### IP66 Twin 13A Double Pole Switched Socket

#### Technical Features

##### Electric current

Rated current	13 A
---------------	------

##### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

##### Materials

Colour	Light grey
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

##### Dimensions

Height	116.50 mm
Width	146 mm
Depth	88.25 mm

##### Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

##### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

##### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No

##### Accessories

Has labelling field	No
---------------------	----

##### Cover, door

Type of lid	Hinged cover falls back, manual clip-in
-------------	---

##### Capacity

Number of modules	0
-------------------	---

##### Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

##### Functions

With orientation lighting	No
With function lighting	No

##### Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes