



KDN263AZS

10mod Busbar 2P with 1mod space with auxiliary (Aux1/2mod- LN-space)

Technical Features

Electric current

Rated current 63 A

Architecture

Number of poles 2

Dimensions

Length 185 mm

Voltage

Rated impulse withstand voltage Uimp 4000 V

Rated operational voltage Ue 230 - 400 V

Connection

Cross-section rigid conductor 10 mm²

Connector/plug type Phase busbar with fork

Capacity

Number of modules 10.50

Sustainability

REACH-SVHC free Yes

RoHS conform Yes