



FL714L

Steel enclosure, Orion.Tech, plain door 600x400x200 mm

Technical Features

Dimensions

Height	600 mm
Width	400 mm
Depth	250 mm
Thickness of sidewall	1 mm

Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class I
Locking type	Barrel lock Key lock
Impact resistance IK	IK10

Equipment

Number of flange plate openings	2
---------------------------------	---

Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	No

Materials

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

Cover, door

Number of cabinet doors	1
Door/cover is transparent	No

Electric current

Rated current	630 A
---------------	-------

Sustainability

RoHS conform	Yes
--------------	-----