



FL713L

**Steel enclosure, Orion.Tech, plain door 500x400x200 mm**

**Technical Features**

**Dimensions**

|                       |        |
|-----------------------|--------|
| Height                | 500 mm |
| Width                 | 400 mm |
| Depth                 | 200 mm |
| Thickness of sidewall | 1 mm   |

**Safety**

|                               |                         |
|-------------------------------|-------------------------|
| Ingress Protection (IP) class | IP65                    |
| Protection class              | Isolation class I       |
| Locking type                  | Barrel lock<br>Key lock |
| Impact resistance IK          | IK10                    |

**Equipment**

|                                 |   |
|---------------------------------|---|
| Number of flange plate openings | 2 |
|---------------------------------|---|

**Installation, mounting**

|                            |               |
|----------------------------|---------------|
| Mounting on                | Wall mounting |
| Suitable for outdoor usage | No            |

**Materials**

|           |               |
|-----------|---------------|
| Colour    | Light grey    |
| RAL code  | 7035          |
| Treatment | Powder coated |
| Material  | Steel         |

**Equipment**

|                |   |
|----------------|---|
| Number of rows | 1 |
|----------------|---|

**Cover, door**

|                           |    |
|---------------------------|----|
| Number of cabinet doors   | 1  |
| Door/cover is transparent | No |

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 630 A |
|---------------|-------|

**Sustainability**

|              |     |
|--------------|-----|
| Halogen free | Yes |
| RoHS conform | Yes |