



FL715L

**Steel enclosure, Orion.Tech, plain door 600x400x250 mm**

**Technical Features**

**Dimensions**

Height	600 mm
Width	400 mm
Depth	250 mm
Thickness of sidewall	1 mm

**Safety**

Ingress Protection (IP) class	IP65
Protection class	Isolation class I
Locking type	Barrel lock Key lock
Impact resistance IK	IK10

**Equipment**

Number of flange plate openings	2
---------------------------------	---

**Installation, mounting**

Mounting on	Wall mounting
Suitable for outdoor usage	No

**Materials**

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

**Cover, door**

Number of cabinet doors	1
Door/cover is transparent	No

**Electric current**

Rated current	630 A
---------------	-------

**Sustainability**

Halogen free	Yes
RoHS conform	Yes