



WMGS16BSB

20A Intermediate Switch Brushed Steel Black Insert

Technical Features

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour Stainless steel

Surface finish Matt

Material Duroplastic
Stainless steel

Treatment Brushed

Identification

Assembly arrangement Basic element with central cover plate

Connectivity

Mounting type Snap-on mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 59 x 25 mm

Built-in depth 13.10 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Single rocker

Electric current

Rated current 20 A

Texts

Lighting Without lighting (cannot be illuminated)

Switch mode Intermediate

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes