

Industrial contactor 40A-AC3 / coil 240V AC 50 Hz

Technical Features

Architecture

Type of pole	3P
--------------	----

Voltage

Rated operational voltage Ue	660 - 660 V
Command voltage AC	240 - 240 V
Command voltage DC	0 - 0 V
Rated insulation voltage Ui	1000 V

Electric current

Rated operational current le under 3P 220 - 230 V AC3 according to IEC 60947 - 4	42 A
Acceptable current rating AC3	40 A
Rated operational current le under 3P 380 - 400 V AC AC3 according to IEC 60947 - 4	40 A

Dimensions

Depth	112 mm
-------	--------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

Rated operational power for 3P under 220 - 230 V AC AC3 according to IEC 60947 - 4	11 kW
--	-------

Endurance

Number of mechanical operations	5000000
Electric endurance in number of cycles	500000

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Equipment

Number of auxiliary contacts as normally open contact	1
Number of auxiliary contacts as normally closed contact	1
Number of NO contacts	3
Number of NC contacts	0

Use conditions

Operating temperature	-20 - 55 °C
Storage/transport temperature	-40 - 80 °C

Connection

Cross-section of input and output with screws, for flexible conductors	6 - 16 mm ²
Cross-section of input and output with screws, for massive conductors	6 - 16 mm ²

Sustainability

RoHS conform	Yes
--------------	-----