



EPN053

Auxiliary for control by maintained contact

Technical Features

Electric current

Rated current	2 A
---------------	-----

Capacity

Number of modules	0.50
-------------------	------

Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Connection

Cross-section flexible conductor	1 - 6 mm ²
----------------------------------	-----------------------

Cross-section rigid conductor	1.5 - 10 mm ²
-------------------------------	--------------------------

Power

Total power loss under IN	0.10 W
---------------------------	--------

Dimensions

Height	85 mm
--------	-------

Width	8.90 mm
-------	---------

Depth	64 mm
-------	-------