



WXF112

**USB charger gallery**

**Technical Features**

**Capacity**

Number of modules	2
-------------------	---

**Connectivity**

Type of connection	Screw terminal
Connector/plug type USB	A

**Dimensions**

Height	40 mm
Width	40 mm
Depth	32 mm
Built-in depth flush-mounted boxes	32 mm

**Equipment**

Number of outputs	2
-------------------	---

**Accessories**

With miniature fuse	No
---------------------	----

**Materials**

Colour	Black
RAL code	7021
Material	Polycarbonate (PC)

**Power**

Output power	15 W
--------------	------

**Voltage**

Input voltage	230 - 230 V
Output voltage	5 - 5 V

**Electric current**

Rated current	3 A
Output current	3000 mA

**Texts**

Connectors jacks	With 2 USB sockets type A
Fuse	Short-circuit and overload-proof (electronic fuse)

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes