



WBSP2S

**Silhouette 10A twin socket Horz+ shutter**

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Rated current	10 A
---------------	------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC) Thermoplastic
Treatment	Untreated

**Dimensions**

Height	77 mm
Width	117 mm
Depth	33 mm
Built-in depth flush-mounted boxes	23 mm
Built-in depth	23 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting

**Equipment**

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	No
---------------------	----

**Cover, door**

Type of lid	Without lid
-------------	-------------

**Capacity**

Number of modules	2
-------------------	---

**Safety**

With enhanced contact protection	Yes
Impact resistance IK	IK08
Ingress Protection (IP) class	IP20

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

---

**Texts**

Cover	Full cover plate
Protection	Enhanced contact protection
Type of connection	With screw terminals

---

**Suitable for**

silhouette

---

**Sustainability**

RoHS conform	Yes
--------------	-----