



286710



**Tronic rotary dimmer, house electronics**

**Technical Features**

**Voltage**

Operating voltage 230 - 230 V

**Frequency**

Frequency 50 - 50 Hz

**Materials**

Material Metal Plastic

**Dimensions**

Diameter axis 4 mm

Height 71 mm

Width 71 mm

Depth 50 mm

**Architecture**

Control/operation element Push & rotative switch

**Texts**

Dimming principle Phase cut-off

Fuse Short-circuit and overload-proof (electronic fuse)

Installation mode With spreader claws

Type of connection With screw terminals

**Equipment**

Substation input No

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes