



286710



Tronic rotary dimmer, house electronics

Technical Features

<b>Voltage</b>	
Operating voltage	230 - 230 V
<b>Frequency</b>	
Frequency	50 - 50 Hz

<b>Materials</b>	
Material	Metal Plastic

<b>Dimensions</b>	
Diameter axis	4 mm
Height	71 mm
Width	71 mm
Depth	50 mm

<b>Architecture</b>	
Control/operation element	Push & rotative switch

<b>Texts</b>	
Dimming principle	Phase cut-off
Fuse	Short-circuit and overload-proof (electronic fuse)
Installation mode	With spreader claws
Type of connection	With screw terminals

<b>Sustainability</b>	
REACH-SVHC free	Yes
RoHS conform	Yes