



41097006



SCHUKO soc.out. LEDorient.,enhncd contact prot.,screw-in lift term.,K1,ant.,lacq

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Anthracite
RAL code 7021
Surface finish Matt
Material Thermoplastic
Treatment Untreated
Varnished

Dimensions

Height 71 mm
Width 71 mm
Number of units 1
Built-in depth 32 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal
Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO
Rotated central insert No
With hinged lid No
With round protective earth pin No
With signal lamp No
With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Controls and indicators

Type of lighting for the installation devices Integrated orientation light

Safety

With enhanced contact protection Yes
Impact resistance IK IK05
Ingress Protection (IP) class IP20

Functions

With orientation lighting Yes
With function lighting No

Identification

With imprint No

Texts

Cover	Central cover plate
Lighting	Additional benefit by combination of a socket outlet with an orientation light
Wiring	Through-wiring possible, therefore also ideal for retrofitting
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

Suitable for

K.x

Sustainability

RoHS conform	Yes
--------------	-----