



41097004



## SCHUKO soc.out. LED orient.,enhncd contact prot.,screw-in lift ,K5,steel,lacq

### Technical Features

#### Electric current

Rated current	16 A
---------------	------

#### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Materials

Colour	Stainless steel
RAL code	9022
Surface finish	Matt
Material	Stainless steel Thermoplastic
Treatment	Untreated Varnished

#### Dimensions

Height	71 mm
Width	71 mm
Number of units	1
Built-in depth	32 mm

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

#### Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

#### Accessories

Has labelling field	No
---------------------	----

#### Capacity

Number of modules	1
-------------------	---

#### Controls and indicators

Type of lighting for the installation devices	Integrated orientation light
---	------------------------------

#### Safety

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

#### Functions

With orientation lighting	Yes
With function lighting	No

<b>Texts</b>		
Imprint		Without imprint
Cover		Central cover plate
Lighting	Additional benefit by combination of a socket outlet with an orientation light	
Wiring	Through-wiring possible, therefore also ideal for retrofitting	
Protection		Enhanced contact protection
Type of connection		With screw-in lift terminals

<b>Suitable for</b>		
K.x		

<b>Sustainability</b>		
RoHS conform		Yes