



BR7013019010

Wall trunking base C-profile BR 70x130mm of PVC in pure white

Technical Features

Dimensions

Height	68 mm
Width	130 mm
Length	2000 mm

Cover, door

Number of mountable lids	1
Cover width 1	100 mm
Cover width 2	0 mm
Cover width 3	0 mm

Dimensions

Inner cross-section	7580 - 7580 mm ²
---------------------	-----------------------------

Capacity

Max. number of cables (Ø11 mm, 50% filled, with devices)	16
Max. number of cables (Ø11mm, 50% filled, without devices)	31

Compatibility

Device installation compatible format	Standard 60 mm, 45 mm, CEE, EIB, MCBs
---------------------------------------	---------------------------------------

Installation, mounting

Base perforation	Yes
------------------	-----

Materials

Material	Polyvinylchloride (PVC)
Treatment	Untreated
Colour	Pure white
RAL code	9010

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP30

Use conditions

Operating temperature	-5 - 60 °C
-----------------------	------------

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Equipment

Cable retaining clip included	No
Number of cable retainers per meter	0
With protective film	Yes

Illustrations | Drawings

