



WGDL121NP-12V

12V 2G press switch with led

Technical Features

Electric current

Switching current 10 A

Voltage

Rated voltage 250 V

Architecture

Control/operation element Double rocker

Materials

Colour White

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

Transparent No

Dimensions

Height 90 mm

Width 90 mm

Depth 25 mm

Controls and indicators

Number of buttons 2

Connectivity

Type of connection Screw terminal

Safety

Ingress Protection (IP) class IP20

Texts

Switch mode 1-way

Suitable for

shark

Sustainability

RoHS conform Yes