



KB263C

Insulated busbar 2P 63A prong 10mm² 24M

Technical Features

Electric current

Rated current 63 A

Architecture

Number of poles 2

Dimensions

Length 420 mm

Voltage

Rated impulse withstand voltage Uimp 4000 V

Rated operational voltage Ue 230 - 400 V

Connection

Cross-section rigid conductor 10 mm²

Connector/plug type Phase busbar with pin

Capacity

Number of modules 24

Sustainability

RoHS conform Yes