



KB263C

**Insulated busbar 2P 63A prong 10mm<sup>2</sup> 24M**

**Technical Features**

**Electric current**

Rated current	63 A
---------------	------

**Architecture**

Number of poles	2
-----------------	---

**Dimensions**

Length	420 mm
--------	--------

**Voltage**

Rated impulse withstand voltage Uimp	4000 V
Rated operational voltage Ue	230 - 400 V

**Connection**

Cross-section rigid conductor	10 mm <sup>2</sup>
Connector/plug type	Phase busbar with pin

**Capacity**

Number of modules	24
-------------------	----

**Sustainability**

RoHS conform	Yes
--------------	-----