



GD218A

Enclosure,gamma,surface mounting,36Modules, version France

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	2
Number of rows	2
Number of section in width	1
With lock	No

Capacity

Number of modules	36
-------------------	----

Dimensions

Height	375 mm
Width	355 mm
Depth	103 mm

Cover, door

Number of cabinet doors	0
Number of locks	0

Dimensions

Number of width units	18
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Equipment

Has mounting plate	Yes
--------------------	-----

Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Without lock
Glow wire test	850 °C

Sustainability

RoHS conform	Yes
--------------	-----