



286610

### Technical Features

#### Voltage

Operating voltage	230 - 230 V
-------------------	-------------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Materials

Material	Metal Plastic
----------	------------------

#### Dimensions

Diameter axis	4 mm
Height	71 mm
Width	71 mm

#### Architecture

Control/operation element	Push & rotative switch
---------------------------	------------------------

#### Texts

Dimming principle	Phase cut-on
Fuse	Short-circuit and overload-proof (fine-wire fuse)
Installation mode	With spreader claws
Type of connection	With screw terminals

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes