

3 Phase KWhmeter 80A

**Technical Features**

**Architecture**

Type of pole	3P+N
--------------	------

**Electric current**

Rated current	80 A
---------------	------

**Capacity**

Number of modules	7
-------------------	---

**Connectivity**

Type of connection	Direct connection
--------------------	-------------------

**Dimensions**

Height	107 mm
Width	126 mm
Depth	58 mm

**Equipment**

Type of pulse generator	Electrical
-------------------------	------------

**Installation, mounting**

Mounting on	DIN rail
-------------	----------

**Measurement**

Type of measuring instrument	Electronic
Frequency measuring range	50 - 60 Hz

**Power supply**

Number of phases for power supply	4
-----------------------------------	---

**Safety**

Ingress Protection (IP) class	IP30
-------------------------------	------

**Use conditions**

Operating temperature	-5 - 45 °C
Storage/transport temperature	-20 - 70 °C

**Power**

Power consumption VA	9.70 VA
Total power loss under IN	2 W

**Electric current**

Maximum measuring circuit current	80 A
-----------------------------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------