



WGDT2RJ6IG

RJ45 outlet cat6 (2mod);ig

Technical Features

Frequency

Transmission bandwidth	0-250 MHz
------------------------	-----------

Equipment

With transparent label holder	No
-------------------------------	----

Number of outputs	2
-------------------	---

Use conditions

Operating temperature	-20 - 45 °C
-----------------------	-------------

Equipment

With hinged lid	No
-----------------	----

Materials

Colour	Interstellar grey
--------	-------------------

Connection

Connector/plug type	RJ45
---------------------	------

Materials

Material	Polycarbonate (PC)
----------	--------------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Voltage

Rated voltage	0 V
---------------	-----

Electric current

Rated current	0 A
---------------	-----

Dimensions

Built-in depth	27 mm
----------------	-------

Texts

Outlet	With straight outlet
--------	----------------------

Protection	With dust protection sliders
------------	------------------------------

Supporting plate/supporting ring	With supporting plate
----------------------------------	-----------------------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----