



EG103V



Weekly time switch 1 channel, 12/24V, digital, 2 modules

Technical Features

Voltage

Rated operational voltage U _e	12 - 24 V
--	-----------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

230 V incandescent and halogen lamp	2300 W
-------------------------------------	--------

Functions

Power reserve in years	5 y
With network synchronisation	No
With quartz synchronisation	Yes
Number of function channels	1

Equipment

Accuracy per day	1.50 s
With impulse programme	Yes
Number of channels	1

Connection

Type of contacts	1x changeover
------------------	---------------

Settings

Daily programme	Yes
Weekly programme	No
Annual programme	No

Use conditions

Operating temperature	-5 - +45 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	1 - 16 mm ²
Cross-section rigid conductor	1 - 6 mm ²

Texts

Type of connection	With screw terminals
Function	Keylock by means of blocking key With pulse function

Dimensions

Height	85 mm
Width	35 mm
Depth	64 mm

Main electrical attributes

Minimum interval between 2 switching times	1 min
--	-------

Capacity

Number of modules	2
-------------------	---