



WNA036

cubyko Key switch 3 positions composable grey IP55

Technical Features

Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Satin finish
Material	Polypropylene (PP)
Treatment	Varnished

Identification

Assembly arrangement	Mechanism with upper casing
----------------------	-----------------------------

Connectivity

Mounting type	Click mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	75 x 75 mm
Built-in depth flush-mounted boxes	40 mm

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK07

Architecture

Control/operation element	Key
---------------------------	-----

Electric current

Rated current	10 A
---------------	------

Connection

Connector/plug type	Turn screw lock
---------------------	-----------------

Texts

Lighting	Without lighting (cannot be illuminated)
----------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes