



WNA100B



IP55

**cubyko Socket 2P+E composable white IP55**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Use conditions**

Operating temperature -15 - 30 °C

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Polar white

RAL code 9010

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Contains recycled material (% of total plastic weight) 0 %

**Dimensions**

Height 71 mm

Width 71 mm

Depth 22.80 mm

Number of units 1

Built-in depth flush-mounted boxes 0 mm

Built-in depth 22 mm

Height of P-touch band for labelling field 0 mm

**Connection**

Connector/plug type Turn screw lock

Cross-section flexible conductor without wire end sleeve 1.0 - 2.5 mm<sup>2</sup>

**Installation, mounting**

Mounting on Flush mounting  
Surface mounting

Mounting-/Connection Position Horizontal

**Connectivity**

Type of connection Plug-in connection

With claw mounting No

Mounting type Screw mounting

**Equipment**

Connector/plug type socket outlet Earthing pin

Rotated central insert No

With hinged lid Yes

With round protective earth pin Yes

With signal lamp No

With lock No

**Accessories**

Has labelling field No

Pre-equipped with Socket outlet

**Cover, door**

Type of lid Self-closing hinged cover, can be arrested in end position

---

**Capacity**

Number of modules	1
-------------------	---

---

**Safety**

With enhanced contact protection	Yes
----------------------------------	-----

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP55
-------------------------------	------

Usable in higher IP class	IP55 with closed cover
---------------------------	------------------------

---

**Functions**

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

---

**Identification**

With imprint	No
--------------	----

---

**Texts**

Cover	Complete housing
-------	------------------

Protection	Enhanced contact protection
------------	-----------------------------

Type of connection	With plug-in terminals
--------------------	------------------------

Labelling	Without labelling
-----------	-------------------

---

**Suitable for**

cubyko	
--------	--

---

**Sustainability**

Halogen free	Yes
--------------	-----

RoHS conform	Yes
--------------	-----