



FU52DN

Enclosure, NewVegaD, 987x550x150mm, 120 modules, flush-mounted, distribution

**Technical Features**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Flush mounting

**Electric current**

Rated current	160 A
---------------	-------

**Equipment**

Number of rails	5
Number of rows	5
Number of section in width	2
With lock	No
Has neutral terminal block	No

**Capacity**

Number of modules	120
-------------------	-----

**Dimensions**

Height	987 mm
Width	600 mm
Depth	150 mm
Built-in width	550 mm
Built-in depth	110 mm
Number of width units	24

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Connection**

Number of conduit inlets	4
--------------------------	---

**Materials**

Material	Metal Plastic
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	No
Has mounting plate	No

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Without lock

**Sustainability**

RoHS conform	Yes
--------------	-----