



Technical Features

Operating voltage	230 - 230 V
-------------------	-------------

Frequency	50 - 60 Hz
-----------	------------

Material	Metal	Plastic
----------	-------	---------

Diameter axis	4 mm
Built-in depth	24 mm
Height	71 mm
Width	71 mm
Depth	43 mm

Control/operation element	Push & rotative switch
---------------------------	------------------------

Power consumption standby	0.30 W
---------------------------	--------

Voltage	Voltage test possible without dismantling
Installation mode	With spreader claws
Type of connection	With plug-in terminals
Operation and control	No Bluetooth interface

REACH-SVHC free	Yes
RoHS conform	Yes