



296210



Extension unit insert for universal rotary dimmer comfort, soft-l., light cont.

#### Technical Features

##### Voltage

Operating voltage 230 - 230 V

##### Frequency

Frequency 50 - 60 Hz

##### Materials

Material Metal  
Plastic

##### Dimensions

Diameter axis 4 mm

Built-in depth 24 mm

Height 71 mm

Width 71 mm

Depth 43 mm

##### Architecture

Control/operation element Push & rotative switch

##### Power

Power consumption standby 0.30 W

##### Texts

Voltage Voltage test possible without dismantling

Installation mode With spreader claws

Type of connection With plug-in terminals

Operation and control No Bluetooth interface

##### Sustainability

REACH-SVHC free Yes

RoHS conform Yes