



VML\_SIZE\_6

**Consumer unit, Design 10, 12 way, multi tariff, 6+5+1, 2\*100A sw, 1\*63A,**

**Technical Features**

**Installation, mounting**

Mounting on Surface mounting

**Functions**

Has protection main switch Yes  
 Overvoltage protection No

**Capacity**

Number of modules 12

**Electric current**

Rated current 100 A

**Dimensions**

Depth 100 mm  
 Height 245 mm  
 Width 404.20 mm  
 Number of width units 12

**Cover, door**

Interlockable No  
 Door/cover is transparent No

**Materials**

RAL code 9010  
 Colour Pure white  
 Material Steel

**Connection**

Number of accessible phases 1

**Scope of delivery**

Number of RCCB in enclosure 2

**Equipment**

Number of rows 1  
 Number of rails 1  
 With socket outlet No

**Safety**

Ingress Protection (IP) class IP2XC  
 Number of earth leakage switches 300 mA 0

**Sustainability**

REACH-SVHC free Yes  
 RoHS conform Yes