



WGDL131NPNB

10A 3G press switch with led;nb

Technical Features

Electric current

|                   |      |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Triple rocker |
|---------------------------|---------------|

Materials

|                |                    |
|----------------|--------------------|
| Colour         | Bronze             |
| Surface finish | Matt               |
| Material       | Polycarbonate (PC) |
| Treatment      | Varnished          |
| Transparent    | No                 |

Dimensions

|                                    |       |
|------------------------------------|-------|
| Height                             | 86 mm |
| Width                              | 86 mm |
| Depth                              | 25 mm |
| Built-in depth flush-mounted boxes | 35 mm |

Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 3 |
|-------------------|---|

Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Texts

|             |       |
|-------------|-------|
| Switch mode | 1-way |
|-------------|-------|

Suitable for

|       |  |
|-------|--|
| shark |  |
|-------|--|

Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|