



KB280B

### Insulated busbar 2P 80A prong 16mm<sup>2</sup> 57M

#### Technical Features

##### Electric current

Rated current	80 A
---------------	------

##### Architecture

Number of poles	2
-----------------	---

##### Dimensions

Length	1000 mm
--------	---------

##### Voltage

Rated impulse withstand voltage Uimp	4000 V
--------------------------------------	--------

Rated operational voltage Ue	230 - 400 V
------------------------------	-------------

##### Connection

Cross-section rigid conductor	16 mm <sup>2</sup>
-------------------------------	--------------------

Connector/plug type	Phase busbar with pin
---------------------	-----------------------

##### Capacity

Number of modules	57
-------------------	----

##### Sustainability

RoHS conform	Yes
--------------	-----